



We sweat the details so you don't have to.

The FB5CPM (inlet) and FB6CPM (outlet) air loaded sanitary constant pressure modulating valves are clearly the preferred choice in HTST/UHT pasteurization. Take a quick look to see how our CPM valves compare to the others and then contact us at foodandbev@richardsind.com or visit our website at SteriflowFoodandBev.com.



	FB CPM SERIES	OTHER
3A Approval	✓	✓
Leak detection port	✓	✓
Optional end connections	✓	✓
Lifetime Jorlon diaphragm warranty	✓	✗
Single diaphragm design	✓	✗
Stem guiding above diaphragm	✓	✗
Large diaphragm for optimal sensitivity to pressure changes	✓	✗
Bolted bonnet	✓	✗
Optional seat material for Class VI shutoff	✓	✗
Maximum operating pressure of 200 psi	✓	✗
Maximum temperature of 300°F	✓	✗